


PRODUCT-DETAILS

3GBA092510-BEC

IE2 High Efficiency Cast Iron Motors, 1.5 kW, 500 V (3GBA092510-BEC)



General Information	
Product ID	3GBA092510-BEC
ABB Type Designation	M2BAX 90LA 4
Catalog Description	IE2 High Efficiency Cast Iron Motors, 1.5 kW, 500 V (3GBA092510-BEC)

Ordering	
ABB Type Designation	M2BAX 90LA 4
Invoice Description	M2BAX 90LA 4
Product Name	3-Phase squirrel cage motor
Product Type	EBA2__M2BAX_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN) Poland (PL)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Menden, Germany

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	500 V	1.50 kW	1435 r/min	2.70 A	0.770	82.80 %	10.02 N·m	6.50
D	--	60 Hz	575 V	1.50 kW	1748 r/min	2.42 A	0.740	84.00 %	8.26 N·m	7.70

Connection Configuration	D
Temperature Class Default	--
Input Voltage (U _{in})	500 V
Frequency (f)	50 Hz
Output Power	1.5 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2
IE Class Data (60 Hz)	IE Class IE2
	Full Load (100%) 84.0 %
	Partial Load (75%) 84.0 %
	Partial Load (50%) 82.1 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	No
Type of Duty	S1
Voltage Code	E

Mechanical

Frame Size	90
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	24 kg
Gross Weight	27 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	d19446d4-4db6-4ddb-826d-2341a0f7dd46 Finland (FI)

Classifications

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE2 High Efficiency Cast Iron Motors

