



PRODUCT-DETAILS

3GBA092510-BSCCNKA  
M2BAX 90LA4

General Information					
Product ID	3GBA092510-BSCCNKA				
ABB Type Designation	M2BAX 90LA 4				
Catalog Description	M2BAX 90LA4				
Additional Information					
ABB Type Designation	M2BAX 90LA 4				
Altitude	1000 m				
Ambient Temperature	40 °C				
Country of Origin	China (CN)				
Customs Tariff Number	85015100				
Direction of Rotation	Both sides				
Electrical Data					
	Conn	Temp Class	Freq	Voltage	Power
	Y	--	50 Hz	380 V	1.50 kW
Frame Size	90				
IC Class	IC411				
IM Class	IMB5 IM3001				
Insulation Class	ICLF				
Invoice Description	M2BAX 90LA4				
IP Class	IP55				
Made To Order	No				
Minimum Order Quantity	1 piece				
Number of Poles (High)	4				
Order Multiple	1 piece				
Package Level 1 Units	0 carton				
Product Name	3-Phase squirrel cage motor				
Product Type	CBA2__M2BAX_CI				
Quote Only	No				
Selling Unit of Measure	piece				
Standards	IEC 60034-1				
Starting of Motor	Direct Online				
Stocked At (Warehouses)	Shanghai, China				

Temperature Class	--
Default	
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)