



PRODUCT-DETAILS

3GBA093510-BSXPMAA

No Description Available

General Information	
Product ID	3GBA093510-BSXPMAA
ABB Type Designation	M2BAXPM 90LA 6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BAXPM 90LA 6
Altitude	1000 m
Ambient Temperature	40 °C
Country of Origin	China (CN)
Customs Tariff Number	85015100

Electrical Data					
Conn	Temp Class	Freq	Voltage	Power	Speed
Y	--	150 Hz	380 V	5.50 kW	3000 r/min
Frame Material					
Cast Iron					
Frame Size					
90					
Gross Weight					
10 kg					
IC Class					
IC411					
IM Class					
IMB5 IM3001					
Insulation Class					
ICLF					
IP Class					
IP55					
Lubrication					
For life					
Made To Order					
No					
Minimum Order Quantity					
1 piece					
Number of Poles (High)					
6					
Order Multiple					
1 piece					
Package Level 1 Units					
0 carton					
Product Name					
3-Phase squirrel cage motor					
Product Net Weight					
10 kg					
Product Type					
CBA2__M2BAX_CI					
Quote Only					
No					
Selling Unit of Measure					
piece					
Standards					
IEC 60034-1					
Starting of Motor					
Direct Online					

Stocked At (Warehouses)	Shanghai, China
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S