



PRODUCT-DETAILS

3GBA093510-BSXPMTA

No Description Available

General Information	
Product ID	3GBA093510-BSXPMTA
ABB Type Designation	M2BAXPM 90LA 6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BAXPM 90LA 6
Altitude	1000 m
Ambient Temperature	40 °C
Country of Origin	China (CN)
Customs Tariff Number	85015100

Electrical Data					
Conn	Temp Class	Freq	Voltage	Power	Speed
Y	--	150 Hz	380 V	5.50 kW	3000 r/min
Frame Size	90				
Gross Weight	10 kg				
IC Class	IC411				
IM Class	IMB5 IM3001				
Insulation Class	ICLF				
IP Class	IP55				
Lubrication	For life				
Made To Order	No				
Minimum Order Quantity	1 piece				
Number of Poles (High)	6				
Order Multiple	1 piece				
Package Level 1 Units	0 carton				
Product Name	3-Phase squirrel cage motor				
Product Net Weight	10 kg				
Product Type	CBA2__M2BAX_CI				
Quote Only	No				
Selling Unit of Measure	piece				
Standards	IEC 60034-1				
Starting of Motor	Direct Online				
Stocked At	Shanghai, China				

(Warehouses)	
Temperature Class	--
Default	
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S