



PRODUCT-DETAILS

3GBA101510-HSUCN  
M2BAK 100LA2

General Information					
Product ID	3GBA101510-HSUCN				
ABB Type Designation	M2BAK 100LA2				
Catalog Description	M2BAK 100LA2				
Additional Information					
ABB Type Designation	M2BAK 100LA2				
Altitude	1000 m				
Ambient Temperature	40 °C				
Country of Origin	China (CN)				
Customs Tariff Number	85015100				
Direction of Rotation	Both sides				
Electrical Data					
	Conn	Temp Class	Freq	Voltage	Power
	Y	--	50 Hz	380 V	3.00 kW
Frame Size					100
Gross Weight					33 kg
IC Class					IC411
IM Class					IMB35 IM2001
Insulation Class					ICLF
Invoice Description					M2BAK 100LA2
IP Class					IP55
Made To Order					No
Minimum Order Quantity					1 piece
Number of Poles (High)					2
Order Multiple					1 piece
Package Level 1 Units					0 carton
Product Name	3-Phase squirrel cage motor				
Product Net Weight					33 kg
Product Type	CBK2__M2BAK_IE2_CI				
Quote Only					No
Selling Unit of Measure					piece
Standards					IEC 60034-1
Starting of Motor					Direct Online

Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S