



PRODUCT-DETAILS

3GBA103212-BSBCN

No Description Available

General Information	
Product ID	3GBA103212-BSBCN
ABB Type Designation	M2BA 100L 6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 100L 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6206-2Z/C3
Bearing NDE	6205-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	220 V	1.50 kW	945 r/min	6.60 A	0.730	81.40 %	15.10 N·m	3.70
Y	--	50 Hz	380 V	1.50 kW	945 r/min	3.80 A	0.730	81.40 %	15.10 N·m	3.70
D	--	50 Hz	230 V	1.50 kW	950 r/min	6.50 A	0.690	82.20 %	15.00 N·m	4.00

Frame Size	100
Gross Weight	37 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2
	Full Load (100%) 82.2 %
	Partial Load (75%) 82.9 %
	Partial Load (50%) 81.6 %
IE Class Data (60 Hz)	IE Class IE1
	Full Load (100%) 84.7 %
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece

Number of Poles (High)	6
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	37 kg
Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)