



PRODUCT-DETAILS

3GBA113310-BDNIN

IE4 Super Premium Efficiency Cast Iron Motors, 2.2 kW, 415 V (3GBA113310-BDNIN)



General Information	
Product ID	3GBA113310-BDNIN
ABB Type Designation	M2BAX 112MA 6
Catalog Description	IE4 Super Premium Efficiency Cast Iron Motors, 2.2 kW, 415 V (3GBA113310-BDNIN)

Ordering	
ABB Type Designation	M2BAX 112MA 6
Invoice Description	M2BAX 112MA 6
Product Name	3-Phase squirrel cage motor
Product Type	IBA4__M2BAX_IE4_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	India (IN)
Customs Tariff Number	85015220

Electrical	
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	415 V	2.20 kW	965 r/min	5.60 A	0.710	87.40 %	21.55 N·m	5.40
Connection Configuration										D
Temperature Class Default										--
Input Voltage (U _{in})										415 V
Frequency (f)										50 Hz
Output Power										2.2 kW
Altitude										1000 m
Ambient Temperature										50 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE4 Full Load (100%) 87.4 % Partial Load (75%) 87.6 % Partial Load (50%) 86.2 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										6
Two Speed Motor										No
Type of Duty										S1
Voltage Code										D

Mechanical	
Frame Material	Cast Iron
Frame Size	112
Bearing	6207-2Z/C3
Bearing NDE	6206-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions	
Package Level 1 Units	0 carton
Product Net Weight	47 kg
Gross Weight	52 kg

Classifications	
UNSPSC	26101100

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE4 Super Premium Efficiency Cast Iron Motors

