



PRODUCT-DETAILS

3GBA113310-BSCCNKA  
M2BAX 112MA6

General Information

Product ID	3GBA113310-BSCCNKA
ABB Type Designation	M2BAX 112MA 6
Catalog Description	M2BAX 112MA6

Additional Information

ABB Type Designation	M2BAX 112MA 6
Altitude	1000 m
Ambient Temperature	40 °C
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides

Electrical Data

Conn	Temp Class	Freq	Voltage	Power
Y	--	50 Hz	380 V	2.20 kW

Frame Size	112
IC Class	IC411
IM Class	IMB5 IM3001
Insulation Class	ICLF
Invoice Description	M2BAX 112MA6
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Type	CBA2__M2BAX_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China
Temperature Class	--
Default	
Terminator Box Location	D-End top
Two Speed Motor	No

Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)