



PRODUCT-DETAILS

3GBA113410-BDDIN
(3GBA113410-BDDIN)



General Information

Product ID	3GBA113410-BDDIN
ABB Type Designation	M2BAX 112MLA 6
Catalog Description	(3GBA113410-BDDIN)

Ordering

ABB Type Designation	M2BAX 112MLA 6
Invoice Description	M2BAX 112MLA 6
Product Name	3-Phase squirrel cage motor
Product Type	IBA3__M2BAX_IE3_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	India (IN)
Customs Tariff Number	85015220

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	415 V	2.20 kW	952 r/min	5.50 A	0.660	84.30 %	22.10 N·m	5.00
Temperature Class Default										--
Altitude										1000 m
Ambient Temperature										50 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE3 Full Load (100%) 84.3 % Partial Load (75%) 84.4 % Partial Load (50%) 82.5 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										6
Two Speed Motor										No
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Cast Iron
Frame Size	112
Bearing	6206-2Z/C3
Bearing NDE	6205-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	47 kg
Gross Weight	52 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE3 Premium Efficiency Cast Iron Motors

