



PRODUCT-DETAILS

# 3GBA113442-HHB

## No Description Available

General Information																							
Product ID				3GBA113442-HHB																			
ABB Type Designation				M2BA 112 MB 6																			
EAN				3GBA113442-HHB																			
Catalog Description				No Description Available																			
Additional Information																							
ABB Type Designation				M2BA 112 MB 6																			
Altitude				1000 m																			
Ambient Temperature				40 °C																			
Bearing				6206-2Z/C3																			
Bearing NDE				6205-2Z/C3																			
Country of Origin				Spain (ES) India (IN) China (CN)																			
Customs Tariff Number				85015220																			
Direction of Rotation				Both sides																			
EAN				3GBA113442-HHB																			
Electrical Data																							
<table><tr><th>Conn</th><th>Temp Class</th><th>Freq</th><th>Voltage</th><th>Power</th><th>Speed</th><th>Current</th><th>Power Factor</th></tr><tr><td>D</td><td>--</td><td>50 Hz</td><td>415 V</td><td>2.20 kW</td><td>955 r/min</td><td>5.40 A</td><td>0.680</td></tr></table>								Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	D	--	50 Hz	415 V	2.20 kW	955 r/min	5.40 A	0.680
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor																
D	--	50 Hz	415 V	2.20 kW	955 r/min	5.40 A	0.680																
Frame Size				112																			
Gross Weight				46 kg																			
IC Class				IC411																			
IE Class Data (50 Hz)				IE Class IE2 Full Load (100%) 82.4 % Partial Load (75%) 80.6 % Partial Load (50%) 80.2 %																			
IM Class				IMB35 IM2001																			
Insulation Class				ICLF																			
IP Class				IP55																			
Lubrication				For life																			
Made To Order				No																			
Minimum Order Quantity				1 piece																			
Number of Poles (High)				6																			
Package Level 1 Units				0 carton																			
Pre Modified Motor				3GBA113442-AHB																			
Product ID																							
Product Name				3-Phase squirrel cage motor																			

Product Net Weight	44 kg
Product Type	2BA2 _ M2BA _ IE2 _ CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	H
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)