



PRODUCT-DETAILS

3GBA131003-BDB

No Description Available

General Information	
Product ID	3GBA131003-BDB
ABB Type Designation	M2BA132 SC2
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA132 SC2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Country of Origin	India (IN) China (CN)
Customs Tariff Number	85015220
Direction of Rotation	Both sides

Electrical Data					
Conn	Temp Class	Freq	Voltage	Power	Power Factor
D	--	50 Hz	380-420 V	9.30 kW	
Y	--	50 Hz	660-690 V	9.30 kW	
D	--	60 Hz	440-480 V	10.70 kW	0.870
Frame Size					
132					
Gross Weight					
72 kg					
IC Class					
IC411					
IM Class					
IMB5 IM3001					
Insulation Class					
ICLF					
IP Class					
IP55					
Lubrication					
For life					
Made To Order					
No					
Minimum Order Quantity					
1 piece					
Number of Poles (High)					
2					
Package Level 1 Units					
0 carton					
Product Name					
3-Phase squirrel cage motor					
Product Net Weight					
68 kg					
Product Type					
2BA2_M2BA_IE2_CI					

Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)