



PRODUCT-DETAILS

# 3GBA131004-ADB

## No Description Available

General Information									
Product ID	3GBA131004-ADB								
ABB Type Designation	M2BA132 SBB2								
Catalog Description	No Description Available								
Additional Information									
ABB Type Designation	M2BA132 SBB2								
Altitude	1000 m								
Ambient Temperature	40 °C								
Bearing	6208-2Z/C3								
Bearing NDE	6208-2Z/C3								
Country of Origin	India (IN) China (CN)								
Customs Tariff Number	85015220								
Direction of Rotation	Both sides								
Electrical Data									
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Torque
	D	--	50 Hz	380-420 V	7.50 kW	2870 r/min	14.20 A	0.890	25.00 N·m
	Y	--	50 Hz	660-690 V	7.50 kW	2870 r/min	8.20 A	0.890	25.00 N·m
	D	--	60 Hz	440-480 V	8.60 kW	3475 r/min	13.30 A	0.900	
Frame Size	132								
Gross Weight	72 kg								
IC Class	IC411								
IM Class	IMB3 IM1001								
Insulation Class	ICLF								
IP Class	IP55								
Lubrication	For life								
Made To Order	No								
Minimum Order Quantity	1 piece								
Number of Poles (High)	2								
Package Level 1 Units	0 carton								
Product Name	3-Phase squirrel cage motor								
Product Net Weight	68 kg								
Product Type	2BA2__M2BA_IE2_CI								
Quote Only	No								
Selling Unit of Measure	piece								
Standards	IEC 60034-1								

Starting of Motor	Direct Online
Temperature Class	--
Default	
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)