



PRODUCT-DETAILS

3GBA131110-ADCCNKA
M2BAX 132SA2

General Information					
Product ID	3GBA131110-ADCCNKA				
ABB Type Designation	M2BAX 132SA 2				
Catalog Description	M2BAX 132SA2				
Additional Information					
ABB Type Designation	M2BAX 132SA 2				
Altitude	1000 m				
Ambient Temperature	40 °C				
Country of Origin	China (CN)				
Customs Tariff Number	85015100				
Direction of Rotation	Both sides				
Electrical Data					
	Conn	Temp Class	Freq	Voltage	Power
	D	--	50 Hz	380 V	5.50 kW
Frame Size					132
IC Class					IC411
IM Class					IMB3 IM1001
Insulation Class					ICLF
Invoice Description					M2BAX 132SA2
IP Class					IP55
Made To Order					No
Minimum Order Quantity					1 piece
Number of Poles (High)					2
Order Multiple					1 piece
Package Level 1 Units					0 carton
Product Name	3-Phase squirrel cage motor				
Product Type	CBA2__M2BAX_CI				
Quote Only					No
Selling Unit of Measure					piece
Standards					IEC 60034-1
Starting of Motor					Direct Online
Stocked At (Warehouses)					Shanghai, China

Temperature Class	--
Default	
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)