



PRODUCT-DETAILS

# 3GBA131110-ADV CN

## No Description Available

General Information											
Product ID								3GBA131110-ADVCN			
ABB Type Designation								M2BAK132SA2			
Catalog Description								No Description Available			
Additional Information											
ABB Type Designation								M2BAK132SA2			
Altitude								1000 m			
Ambient Temperature								40 °C			
Bearing								6208-2Z/C3			
Bearing NDE								6208-2Z/C3			
Country of Origin								China (CN)			
Customs Tariff Number								85015100			
Direction of Rotation								Both sides			
Electrical Data											
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
	Y	--	50 Hz	660 V	5.50 kW	2920 r/min	6.01 A	0.880	90.80 %	17.99 N·m	39.76
	D	--	50 Hz	380 V	5.50 kW	2920 r/min	10.40 A	0.880	90.80 %	17.99 N·m	93.64
Frame Size											132
Gross Weight											70 kg
IC Class											IC411
IE Class Data (50 Hz)											IE Class IE4 Full Load (100%) 90.9 % Partial Load (75%) 91.3 % Partial Load (50%) 90.8 %
IE Class Data (60 Hz)											IE Class NA
IM Class											IMB3 IM1001
Insulation Class											ICLF
IP Class											IP55
Made To Order											No
Minimum Order Quantity											1 piece
Number of Poles (High)											2

Order Multiple	1 piece
Product Name	3-Phase squirrel cage motor
Product Net Weight	70 kg
Product Type	CBK4__M2BAK_IE4_CI
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D