



PRODUCT-DETAILS

3GBA131220-ADDCNKA
M2BAX 132SMB2

General Information					
Product ID	3GBA131220-ADDCNKA				
ABB Type Designation	M2BAX 132SMB 2				
Catalog Description	M2BAX 132SMB2				
Additional Information					
ABB Type Designation	M2BAX 132SMB 2				
Altitude	1000 m				
Ambient Temperature	40 °C				
Bearing	6208-2Z/C3				
Bearing NDE	6208-2Z/C3				
Country of Origin	China (CN)				
Customs Tariff Number	85015100				
Direction of Rotation	Both sides				
Electrical Data					
	Conn	Temp Class	Freq	Voltage	Power
	D	--	50 Hz	380 V	7.50 kW
Frame Size	132				
Gross Weight	58 kg				
IC Class	IC411				
IM Class	IMB3 IM1001				
Insulation Class	ICLF				
Invoice Description	M2BAX 132SMB2				
IP Class	IP55				
Lubrication	For life				
Made To Order	No				
Minimum Order Quantity	1 piece				
Number of Poles (High)	2				
Order Multiple	1 piece				
Package Level 1 Units	0 carton				
Product Name	3-Phase squirrel cage motor				
Product Net Weight	58 kg				
Product Type	CBA3__M2BAX_CI				
Quote Only	No				

Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)