



PRODUCT-DETAILS

3GBA131445-BHB

No Description Available

General Information	
Product ID	3GBA131445-BHB
ABB Type Designation	M2BA 132 SME 2
EAN	3GBA131445-BHB
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 132 SME 2
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Country of Origin	Spain (ES) India (IN) China (CN)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
EAN	3GBA131445-BHB

Electrical Data							
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	415 V	7.50 kW	2910 r/min	12.90 A	0.900
Frame Size	132						
Gross Weight	77 kg						
IC Class	IC411						
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 89.8 % Partial Load (75%) 90.0 % Partial Load (50%) 89.0 %						
IM Class	IMB5 IM3001						
Insulation Class	ICLF						
IP Class	IP55						
Lubrication	For life						
Made To Order	No						
Minimum Order Quantity	1 piece						
Number of Poles (High)	2						
Package Level 1 Units	0 carton						
Product Name	3-Phase squirrel cage motor						
Product Net Weight	75 kg						

Product Type	2BA2_M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	H
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)