

PRODUCT-DETAILS

# 3GBA132110-BDCIN

## (3GBA132110-BDCIN)



General Information	
Product ID	3GBA132110-BDCIN
ABB Type Designation	M2BAX 132SA 4
Catalog Description	(3GBA132110-BDCIN)

Ordering	
ABB Type Designation	M2BAX 132SA 4
Invoice Description	M2BAX 132SA 4
Product Name	3-Phase squirrel cage motor
Product Type	IBA2__M2BAX_IE2_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	India (IN)
Customs Tariff Number	85015220

Electrical	
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	415 V	5.50 kW	1450 r/min	11.10 A	0.790	87.70 %	36.00 N·m	6.00
Temperature Class										--
Default										
Altitude										1000 m
Ambient Temperature										50 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE2 Full Load (100%) 87.7 % Partial Load (75%) 88.4 % Partial Load (50%) 87.6 %
IE Class Data (60 Hz)										IE Class IE2 Full Load (100%) 89.5 % Partial Load (75%) 89.0 % Partial Load (50%) 88.0 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										4
Two Speed Motor										No
Type of Duty										S1
Voltage Code										D

Mechanical

Frame Material	Cast Iron
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	59 kg
Gross Weight	64 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Classifications

UNSPSC	26101100
--------	----------

---

## Categories

---

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE2 High Efficiency Cast Iron Motors

