



## PRODUCT-DETAILS

# 3GBA132213-BSB

## No Description Available

## "No longer for sale" replaced by 3GBA132310-

### General Information

Product ID	3GBA132213-BSB
ABB Type Designation	M2BA 132SMC 4
Catalog Description	No Description Available

### Additional Information

ABB Type Designation	M2BA 132SMC 4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Country of Origin	India (IN) China (CN)
Customs Tariff Number	85015220

### Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	7.50 kW	1450 r/min	14.50 A	0.810	89.30 %	49.40 N·m	7.20
D	--	50 Hz	230 V	7.50 kW	1450 r/min	25.20 A	0.810	89.30 %	49.40 N·m	7.20
Y	--	60 Hz	460 V	7.50 kW	1760 r/min	12.70 A	0.820	90.50 %	40.88 N·m	8.20

Frame Material	Cast Iron
Frame Size	132
Gross Weight	78 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 89.3 % Partial Load (75%) 90.1 % Partial Load (50%) 90.0 %
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 90.5 % Partial Load (75%) 90.4 % Partial Load (50%) 88.8 %
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4

Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	73 kg
Product Type	2BA2 _ M2BA _ IE2 _ CI
Quote Only	No
Replacement Product ID (NEW)	3GBA132310-BSC
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	Top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)