



PRODUCT-DETAILS

3GBA132213-JSB

No Description Available

General Information											
Product ID	3GBA132213-JSB										
ABB Type Designation	M2BA 132SMC 4										
Catalog Description	No Description Available										
Additional Information											
ABB Type Designation	M2BA 132SMC 4										
Altitude	1000 m										
Ambient Temperature	40 °C										
Bearing	6208-2Z/C3										
Bearing NDE	6208-2Z/C3										
Country of Origin	India (IN) China (CN)										
Customs Tariff Number	85015220										
Direction of Rotation	Both sides										
Electrical Data											
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
	Y	--	50 Hz	400 V	7.50 kW	1450 r/min	14.90 A	0.810	89.30 %	49.30 N·m	5.60
	D	--	50 Hz	230 V	7.50 kW	1450 r/min	25.80 A	0.810	89.30 %	49.30 N·m	5.60
	Y	--	60 Hz	460 V	7.50 kW	1760 r/min	12.60 A	0.820	90.60 %	40.60 N·m	6.70
Frame Size	132										
Gross Weight	75 kg										
IC Class	IC411										
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 89.3 % Partial Load (75%) 90.1 % Partial Load (50%) 90.0 %										
IE Class Data (60 Hz)	IE Class IE2 Full Load (100%) 90.6 %										
IM Class	IMB34 IM2101										
Insulation Class	ICLF										
IP Class	IP55										
Lubrication	For life										
Made To Order	No										
Minimum Order Quantity	1 piece										
Number of Poles (High)	4										
Package Level 1 Units	0 carton										
Product Name	3-Phase squirrel cage motor										

Product Net Weight	73 kg
Product Type	2BA2 _ M2BA _ IE2 _ CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)