



PRODUCT-DETAILS

3GBA132310-ADCCNGA  
M2BAX 132MA4

General Information	
Product ID	3GBA132310-ADCCNGA
ABB Type Designation	M2BAX 132MA4
Catalog Description	M2BAX 132MA4

Additional Information	
ABB Type Designation	M2BAX 132MA4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	380 V	7.50 kW	1453 r/min	15.90 A	0.810	88.70 %	49.10 N·m	6.80
D	--	50 Hz	400 V	7.50 kW	1457 r/min	15.60 A	0.780	88.70 %	49.10 N·m	7.20
Y	--	50 Hz	660 V	7.50 kW	1453 r/min	9.13 A	0.810	88.70 %	49.10 N·m	6.80

Frame Size	132
Gross Weight	68 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 88.7 % Partial Load (75%) 88.6 % Partial Load (50%) 87.5 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
Invoice Description	M2BAX 132MA4
IP Class	IP55
Lubrication	For life
Made To Order	No

Minimum Order Quantity	1 piece
Number of Poles (High)	4
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	68 kg
Product Type	CBA2__M2BAX_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Frequency Converter
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Temperature Rise	105 K
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)