



PRODUCT-DETAILS

3GBA132410-HDDIN  
M2BAX 132MLA 4

General Information

Product ID	3GBA132410-HDDIN
ABB Type Designation	M2BAX 132MLA 4
Catalog Description	M2BAX 132MLA 4

Additional Information

ABB Type Designation	M2BAX 132MLA 4
Altitude	1000 m
Ambient Temperature	50 °C
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Country of Origin	India (IN)
Customs Tariff Number	85015220
Direction of Rotation	Both sides

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	415 V	7.50 kW	1462 r/min	15.40 A	0.750	90.40 %	49.00 N·m	7.00

Frame Material	Cast Iron
Frame Size	132
Gross Weight	89 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 90.4 % Partial Load (75%) 90.9 % Partial Load (50%) 90.3 %
IM Class	IMB35 IM2001
Insulation Class	ICLF
Invoice Description	M2BAX 132MLA 4
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4
Order Multiple	1 piece
Package Level 1 Units	0 carton
Pre Modified Motor	3GBA132410-ADDIN
Product ID	
Product Name	3-Phase squirrel cage motor

Product Net Weight	84 kg
Product Type	IBA3_M2BAX_IE3_CI
Quote Only	No
Selling Unit of Measure	piece
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D