



PRODUCT-DETAILS

3GBA132410-HDYCN
M2BAK 132MA4

General Information	
Product ID	3GBA132410-HDYCN
ABB Type Designation	M2BAK 132MA4
Catalog Description	M2BAK 132MA4

Additional Information	
ABB Type Designation	M2BAK 132MA4
Altitude	1000 m
Ambient Temperature	40 °C
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides

Electrical Data				
Conn	Temp Class	Freq	Voltage	Power
D	--	50 Hz	380 V	7.50 kW
Frame Size	132			
Gross Weight	80 kg			
IC Class	IC411			
IM Class	IMB35 IM2001			
Insulation Class	ICLF			
Invoice Description	M2BAK 132MA4			
IP Class	IP55			
Made To Order	No			
Minimum Order Quantity	1 piece			
Number of Poles (High)	4			
Order Multiple	1 piece			
Package Level 1 Units	0 carton			
Product Name	3-Phase squirrel cage motor			
Product Net Weight	80 kg			
Product Type	CBK3__M2BAK_IE3_CI			
Quote Only	No			
Selling Unit of Measure	piece			
Standards	IEC 60034-1			
Starting of Motor	Direct Online			

Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D