



PRODUCT-DETAILS

# 3GBA132442-HHB

## No Description Available

General Information	
Product ID	3GBA132442-HHB
ABB Type Designation	M2BA 132 SMB 4
EAN	3GBA132442-HHB
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 132 SMB 4
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Country of Origin	Spain (ES) India (IN) China (CN)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
EAN	3GBA132442-HHB

Electrical Data							
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
D	--	50 Hz	415 V	5.50 kW	1460 r/min	10.60 A	0.800

Frame Size	132
Gross Weight	72 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 89.5 % Partial Load (75%) 89.7 % Partial Load (50%) 88.8 %
IM Class	IMB35 IM2001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	4
Package Level 1 Units	0 carton
Pre Modified Motor	3GBA132442-AHB
Product ID	
Product Name	3-Phase squirrel cage motor

Product Net Weight	70 kg
Product Type	2BA2 _ M2BA _ IE2 _ CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	H
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)