



PRODUCT-DETAILS

3GBA132443-JHB

No Description Available

| General Information | |
|----------------------|--------------------------|
| Product ID | 3GBA132443-JHB |
| ABB Type Designation | M2BA 132 SMC 4 |
| EAN | 3GBA132443-JHB |
| Catalog Description | No Description Available |

| Additional Information | |
|------------------------|--|
| ABB Type Designation | M2BA 132 SMC 4 |
| Altitude | 1000 m |
| Ambient Temperature | 40 °C |
| Bearing | 6208-2Z/C3 |
| Bearing NDE | 6208-2Z/C3 |
| Country of Origin | Spain (ES) India (IN) China (CN) |
| Customs Tariff Number | 85015220 |
| Direction of Rotation | Both sides |
| EAN | 3GBA132443-JHB |

| Electrical Data | | | | | | | |
|------------------------|---|-------|---------|---------|------------|---------|--------------|
| Conn | Temp Class | Freq | Voltage | Power | Speed | Current | Power Factor |
| D | -- | 50 Hz | 415 V | 7.50 kW | 1455 r/min | 14.30 A | 0.810 |
| Frame Size | 132 | | | | | | |
| Gross Weight | 75 kg | | | | | | |
| IC Class | IC411 | | | | | | |
| IE Class Data (50 Hz) | IE Class IE2 Full Load (100%) 89.6 % Partial Load (75%) 90.1 % Partial Load (50%) 89.4 % | | | | | | |
| IM Class | IMB34 IM2101 | | | | | | |
| Insulation Class | ICLF | | | | | | |
| IP Class | IP55 | | | | | | |
| Lubrication | For life | | | | | | |
| Made To Order | No | | | | | | |
| Minimum Order Quantity | 1 piece | | | | | | |
| Number of Poles (High) | 4 | | | | | | |
| Package Level 1 Units | 0 carton | | | | | | |
| Product Name | 3-Phase squirrel cage motor | | | | | | |
| Product Net Weight | 73 kg | | | | | | |

| | |
|------------------------------|--|
| Product Type | 2BA2_M2BA_IE2_CI |
| Quote Only | No |
| Selling Unit of Measure | piece |
| Standards | IEC 60034-1 |
| Temperature Class Default | -- |
| Terminator Box Location | D-End top |
| Two Speed Motor | No |
| Type of Duty | S1 |
| UNSPSC | 26101100 |
| Voltage Code | H |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |