



PRODUCT-DETAILS

3GBA133004-BDB

No Description Available

General Information	
Product ID	3GBA133004-BDB
ABB Type Designation	M2BA 132 MC6
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 132 MC6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Country of Origin	India (IN) China (CN)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Torque
D	--	50 Hz	380-420 V	5.50 kW	970 r/min	12.20 A	0.730	54.00 N·m
Y	--	50 Hz	660-690 V	5.50 kW	970 r/min	7.04 A	0.730	54.00 N·m
D	--	60 Hz	440-480 V	6.40 kW	1165 r/min	12.00 A	0.760	52.00 N·m

Frame Size	132
Gross Weight	66.38 kg
IC Class	IC411
IM Class	IMB5 IM3001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	65 kg

Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)