



PRODUCT-DETAILS

3GBA133110-ASVCN

No Description Available

General Information											
Product ID	3GBA133110-ASVCN										
ABB Type Designation	M2BAK132SA6										
Catalog Description	No Description Available										
Additional Information											
ABB Type Designation	M2BAK132SA6										
Altitude	1000 m										
Ambient Temperature	40 °C										
Bearing	6208-2Z/C3										
Bearing NDE	6208-2Z/C3										
Country of Origin	China (CN)										
Customs Tariff Number	85015100										
Direction of Rotation	Both sides										
Electrical Data											
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
	D	--	50 Hz	220 V	3.00 kW	965 r/min	12.34 A	0.710	87.70 %	29.69 N·m	86.39
	Y	--	50 Hz	380 V	3.00 kW	965 r/min	7.15 A	0.710	87.70 %	29.69 N·m	50.05
Frame Size	132										
Gross Weight	65 kg										
IC Class	IC411										
IE Class Data (50 Hz)	IE Class IE4 Full Load (100%) 88.6 % Partial Load (75%) 88.8 % Partial Load (50%) 87.7 %										
IE Class Data (60 Hz)	IE Class NA										
IM Class	IMB3 IM1001										
Insulation Class	ICLF										
IP Class	IP55										
Made To Order	No										
Minimum Order Quantity	1 piece										
Number of Poles (High)	6										
Order Multiple	1 piece										
Product Name	3-Phase squirrel cage motor										
Product Net Weight	65 kg										
Product Type	CBK4 M2BAK IE4 CI										
Quote Only	No										

Selling Unit of Measure	piece
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class	--
Default	
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S