



PRODUCT-DETAILS

3GBA133110-BSUCN
M2BAK 132SA6

General Information

Product ID	3GBA133110-BSUCN
ABB Type Designation	M2BAK 132SA6
Catalog Description	M2BAK 132SA6

Additional Information

ABB Type Designation	M2BAK 132SA6
Altitude	1000 m
Ambient Temperature	40 °C
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides

Electrical Data

Conn	Temp Class	Freq	Voltage	Power
Y	--	50 Hz	380 V	3.00 kW

Frame Size	132
Gross Weight	55 kg
IC Class	IC411
IM Class	IMB5 IM3001
Insulation Class	ICLF
Invoice Description	M2BAK 132SA6
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	55 kg
Product Type	CBK2 M2BAK IE2 CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class	--

Default	
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)