



PRODUCT-DETAILS

3GBA133210-ASDCNKA
M2BAX 132SMA6

General Information

Product ID	3GBA133210-ASDCNKA
ABB Type Designation	M2BAX 132SMA 6
Catalog Description	M2BAX 132SMA6

Additional Information

ABB Type Designation	M2BAX 132SMA 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides

Electrical Data

Conn	Temp Class	Freq	Voltage	Power
D	--	50 Hz	380 V	3.00 kW

Frame Size	132
Gross Weight	55 kg
IC Class	IC411
IM Class	IMB3 IM1001
Insulation Class	ICLF
Invoice Description	M2BAX 132SMA6
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	55 kg
Product Type	CBA3__M2BAX_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online

Stocked At (Warehouses)	Shanghai, China
Temperature Class	--
Default	
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)