



PRODUCT-DETAILS

3GBA133320-ADUCN
M2BAK 132MB6

| General Information | | | | | |
|-------------------------|-----------------------------|------------|-------|---------|---------|
| Product ID | 3GBA133320-ADUCN | | | | |
| ABB Type Designation | M2BAK 132MB6 | | | | |
| Catalog Description | M2BAK 132MB6 | | | | |
| | | | | | |
| Additional Information | | | | | |
| ABB Type Designation | M2BAK 132MB6 | | | | |
| Altitude | 1000 m | | | | |
| Ambient Temperature | 40 °C | | | | |
| Country of Origin | China (CN) | | | | |
| Customs Tariff Number | 85015100 | | | | |
| Direction of Rotation | Both sides | | | | |
| Electrical Data | | | | | |
| | Conn | Temp Class | Freq | Voltage | Power |
| | D | -- | 50 Hz | 380 V | 5.50 kW |
| Frame Size | 132 | | | | |
| Gross Weight | 70 kg | | | | |
| IC Class | IC411 | | | | |
| IM Class | IMB3 IM1001 | | | | |
| Insulation Class | ICLF | | | | |
| Invoice Description | M2BAK 132MB6 | | | | |
| IP Class | IP55 | | | | |
| Made To Order | No | | | | |
| Minimum Order Quantity | 1 piece | | | | |
| Number of Poles (High) | 6 | | | | |
| Order Multiple | 1 piece | | | | |
| Package Level 1 Units | 0 carton | | | | |
| Product Name | 3-Phase squirrel cage motor | | | | |
| Product Net Weight | 70 kg | | | | |
| Product Type | CBK2__M2BAK_IE2_CI | | | | |
| Quote Only | No | | | | |
| Selling Unit of Measure | piece | | | | |
| Standards | IEC 60034-1 | | | | |
| Starting of Motor | Direct Online | | | | |

| | |
|------------------------------|--|
| Stocked At (Warehouses) | Shanghai, China Guangzhou, China |
| Temperature Class Default | -- |
| Terminator Box Location | D-End top |
| Two Speed Motor | No |
| Type of Duty | S1 |
| UNSPSC | 26101100 |
| Voltage Code | D |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |