



PRODUCT-DETAILS

3GBA133442-AGB

No Description Available

General Information	
Product ID	3GBA133442-AGB
ABB Type Designation	M2BA 132 SMB 6
EAN	3GBA133442-AGB
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 132 SMB 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Country of Origin	Spain (ES) India (IN) China (CN)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
EAN	3GBA133442-AGB
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
Y	--	50 Hz	415 V	4.00 kW	965 r/min	9.30 A	0.690

Frame Size	132
Gross Weight	71 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 86.0 % Partial Load (75%) 86.3 % Partial Load (50%) 84.7 %
IM Class	IMB3 IM1001
Insulation Class	ICLF
IP Class	IP55
Lubrication	For life
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	6

Package Level 1 Units	0 carton
Product Name	3-Phase squirrel cage motor
Product Net Weight	69 kg
Product Type	2BA2__M2BA_IE2_CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	G
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)