



PRODUCT-DETAILS

3GBA133442-JGB

No Description Available

General Information	
Product ID	3GBA133442-JGB
ABB Type Designation	M2BA 132 SMB 6
EAN	3GBA133442-JGB
Catalog Description	No Description Available

Additional Information	
ABB Type Designation	M2BA 132 SMB 6
Altitude	1000 m
Ambient Temperature	40 °C
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Country of Origin	Spain (ES) India (IN) China (CN)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
EAN	3GBA133442-JGB

Electrical Data							
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
Y	--	50 Hz	415 V	4.00 kW	965 r/min	9.30 A	0.690
Frame Size	132						
Gross Weight	71 kg						
IC Class	IC411						
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 86.0 % Partial Load (75%) 86.3 % Partial Load (50%) 84.7 %						
IM Class	IMB34 IM2101						
Insulation Class	ICLF						
IP Class	IP55						
Lubrication	For life						
Made To Order	No						
Minimum Order Quantity	1 piece						
Number of Poles (High)	6						
Package Level 1 Units	0 carton						
Product Name	3-Phase squirrel cage motor						
Product Net Weight	69 kg						

Product Type	2BA2 _ M2BA _ IE2 _ CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	G
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)