



PRODUCT-DETAILS

# 3GBA133444-HHB

## No Description Available

General Information																								
Product ID	3GBA133444-HHB																							
ABB Type Designation	M2BA 132 SMF 6																							
EAN	3GBA133444-HHB																							
Catalog Description	No Description Available																							
Additional Information																								
ABB Type Designation	M2BA 132 SMF 6																							
Altitude	1000 m																							
Ambient Temperature	40 °C																							
Bearing	6208-2Z/C3																							
Bearing NDE	6208-2Z/C3																							
Country of Origin	India (IN) China (CN)																							
Customs Tariff Number	85015220																							
Direction of Rotation	Both sides																							
EAN	3GBA133444-HHB																							
Electrical Data																								
<table><tr><th>Conn</th><th>Temp Class</th><th>Freq</th><th>Voltage</th><th>Power</th><th>Speed</th><th>Current</th><th>Power Factor</th></tr><tr><td>D</td><td>--</td><td>50 Hz</td><td>415 V</td><td>5.50 kW</td><td>970 r/min</td><td>12.80 A</td><td>0.690</td></tr></table>									Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	D	--	50 Hz	415 V	5.50 kW	970 r/min	12.80 A	0.690
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor																	
D	--	50 Hz	415 V	5.50 kW	970 r/min	12.80 A	0.690																	
Frame Size	132																							
Gross Weight	89 kg																							
IC Class	IC411																							
IE Class Data (50 Hz)	IE Class IE2 Full Load (100%) 86.1 % Partial Load (75%) 83.1 % Partial Load (50%) 84.0 %																							
IM Class	IMB35 IM2001																							
Insulation Class	ICLF																							
IP Class	IP55																							
Lubrication	For life																							
Made To Order	No																							
Minimum Order Quantity	1 piece																							
Number of Poles (High)	6																							
Package Level 1 Units	0 carton																							
Pre Modified Motor	3GBA133444-AHB																							
Product ID																								
Product Name	3-Phase squirrel cage motor																							

Product Net Weight	86 kg
Product Type	2BA2 _ M2BA _ IE2 _ CI
Quote Only	No
Selling Unit of Measure	piece
Standards	IEC 60034-1
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	H
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)