



PRODUCT-DETAILS

3GBA133444-JGB

No Description Available

| General Information | |
|----------------------|--------------------------|
| Product ID | 3GBA133444-JGB |
| ABB Type Designation | M2BA 132 SMF 6 |
| EAN | 3GBA133444-JGB |
| Catalog Description | No Description Available |

| Additional Information | |
|------------------------|--|
| ABB Type Designation | M2BA 132 SMF 6 |
| Altitude | 1000 m |
| Ambient Temperature | 40 °C |
| Bearing | 6208-2Z/C3 |
| Bearing NDE | 6208-2Z/C3 |
| Country of Origin | Spain (ES) India (IN) China (CN) |
| Customs Tariff Number | 85015220 |
| Direction of Rotation | Both sides |
| EAN | 3GBA133444-JGB |
| Electrical Data | |

| Conn | Temp Class | Freq | Voltage | Power | Speed | Current | Power Factor |
|------|------------|-------|---------|---------|-----------|---------|--------------|
| Y | -- | 50 Hz | 415 V | 5.50 kW | 970 r/min | 12.80 A | 0.690 |

| | |
|------------------------|---|
| Frame Size | 132 |
| Gross Weight | 89 kg |
| IC Class | IC411 |
| IE Class Data (50 Hz) | IE Class IE2 Full Load (100%) 86.1 % Partial Load (75%) 83.1 % Partial Load (50%) 84.0 % |
| IM Class | IMB34 IM2101 |
| Insulation Class | ICLF |
| IP Class | IP55 |
| Lubrication | For life |
| Made To Order | No |
| Minimum Order Quantity | 1 piece |
| Number of Poles (High) | 6 |

| | |
|------------------------------|--|
| Package Level 1 Units | 0 carton |
| Product Name | 3-Phase squirrel cage motor |
| Product Net Weight | 86 kg |
| Product Type | 2BA2__M2BA_IE2_CI |
| Quote Only | No |
| Selling Unit of Measure | piece |
| Standards | IEC 60034-1 |
| Temperature Class Default | -- |
| Terminator Box Location | D-End top |
| Two Speed Motor | No |
| Type of Duty | S1 |
| UNSPSC | 26101100 |
| Voltage Code | G |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |