

PRODUCT-DETAILS

3GBA134210-ASKCN

(3GBA134210-ASKCN)



General Information	
Product ID	3GBA134210-ASKCN
ABB Type Designation	M2BAF 132SMA 8
Catalog Description	(3GBA134210-ASKCN)

Ordering	
ABB Type Designation	M2BAF 132SMA 8
Invoice Description	M2BAF 132SMA 8
Product Name	3-Phase squirrel cage motor
Product Type	CBF3__M2BAF_IE3_CI
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	China (CN)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Shanghai, China Guangzhou, China China

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	380 V	2.20 kW	720 r/min	5.75 A	0.710	81.90 %	29.19 N·m	4.60
D	--	50 Hz	220 V	2.20 kW	720 r/min	9.93 A	0.710	81.90 %	29.18 N·m	4.60
Temperature Class										--
Default										
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE3 Full Load (100%) 81.9 % Partial Load (75%) 81.9 % Partial Load (50%) 79.1 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										8
Two Speed Motor										No
Type of Duty										S1
Voltage Code										S

Mechanical

Frame Material	Cast Iron
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	65 kg
Gross Weight	70 kg

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE3 Premium Efficiency Cast Iron Motors

