



PRODUCT-DETAILS

3GBA134210-HDDIN
M2BAX 132SMA 8

General Information	
Product ID	3GBA134210-HDDIN
ABB Type Designation	M2BAX 132SMA 8
Catalog Description	M2BAX 132SMA 8

Additional Information	
ABB Type Designation	M2BAX 132SMA 8
Altitude	1000 m
Ambient Temperature	50 °C
Bearing	6208-2Z/C3
Bearing NDE	6208-2Z/C3
Country of Origin	India (IN)
Customs Tariff Number	85015220
Direction of Rotation	Both sides
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	415 V	2.20 kW	715 r/min	6.10 A	0.610	81.90 %	29.40 N·m	5.00

Frame Material	Cast Iron
Frame Size	132
Gross Weight	74 kg
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3
	Full Load (100%) 81.9 %
	Partial Load (75%) 80.9 %
	Partial Load (50%) 76.4 %
IM Class	IMB35 IM2001
Insulation Class	ICLF
Invoice Description	M2BAX 132SMA 8
IP Class	IP55
Made To Order	No
Minimum Order Quantity	1 piece
Number of Poles (High)	8
Order Multiple	1 piece
Package Level 1 Units	0 carton

Pre Modified Motor	3GBA134210-ADDIN
Product ID	
Product Name	3-Phase squirrel cage motor
Product Net Weight	69 kg
Product Type	IBA3__M2BAX_IE3_CI
Quote Only	No
Selling Unit of Measure	piece
Temperature Class	--
Default	
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D