



PRODUCT-DETAILS

3GBA161310-ADVCN

No Description Available

General Information											
Product ID							3GBA161310-ADVCN				
ABB Type Designation							M2BAK160MA2				
Catalog Description							No Description Available				
Additional Information											
ABB Type Designation							M2BAK160MA2				
Altitude							1000 m				
Ambient Temperature							40 °C				
Bearing							6309-2Z/C3				
Bearing NDE							6309-2Z/C3				
Country of Origin							China (CN)				
Customs Tariff Number							85015100				
Direction of Rotation							Both sides				
Electrical Data											
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
	Y	--	50 Hz	660 V	11.00 kW	2940 r/min	11.68 A	0.890	92.50 %	35.73 N·m	105.09
	D	--	50 Hz	380 V	11.00 kW	2940 r/min	20.30 A	0.890	92.50 %	35.73 N·m	181.78
Frame Size											160
Gross Weight											128 kg
IC Class											IC411
IE Class Data (50 Hz)											IE Class IE4 Full Load (100%) 92.6 % Partial Load (75%) 93.0 % Partial Load (50%) 92.5 %
IE Class Data (60 Hz)											IE Class NA
IM Class											IMB3 IM1001
Insulation Class											ICLF
IP Class											IP55
Made To Order											No
Minimum Order Quantity											1 piece
Number of Poles (High)											2

Order Multiple	1 piece
Product Name	3-Phase squirrel cage motor
Product Net Weight	128 kg
Product Type	CBK4__M2BAK_IE4_CI
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D