



PRODUCT-DETAILS

3GBA162420-HDYCN
M2BAK 160LA4

General Information					
Product ID	3GBA162420-HDYCN				
ABB Type Designation	M2BAK 160LA4				
Catalog Description	M2BAK 160LA4				
Additional Information					
ABB Type Designation	M2BAK 160LA4				
Altitude	1000 m				
Ambient Temperature	40 °C				
Country of Origin	China (CN)				
Customs Tariff Number	85015100				
Direction of Rotation	Both sides				
Electrical Data					
	Conn	Temp Class	Freq	Voltage	Power
	D	--	50 Hz	380 V	15.00 kW
Frame Size	160				
Gross Weight	150 kg				
IC Class	IC411				
IM Class	IMB35 IM2001				
Insulation Class	ICLF				
Invoice Description	M2BAK 160LA4				
IP Class	IP55				
Made To Order	No				
Minimum Order Quantity	1 piece				
Number of Poles (High)	4				
Order Multiple	1 piece				
Package Level 1 Units	0 carton				
Product Name	3-Phase squirrel cage motor				
Product Net Weight	150 kg				
Product Type	CBK3__M2BAK_IE3_CI				
Quote Only	No				
Selling Unit of Measure	piece				
Standards	IEC 60034-1				
Starting of Motor	Direct Online				

Stocked At (Warehouses)	Shanghai, China Guangzhou, China
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D