



PRODUCT-DETAILS

3GBA163410-ADCCNKA
M2BAX 160MLA6

General Information	
Product ID	3GBA163410-ADCCNKA
ABB Type Designation	M2BAX 160MLA 6
Catalog Description	M2BAX 160MLA6

Additional Information	
ABB Type Designation	M2BAX 160MLA 6
Altitude	1000 m
Ambient Temperature	40 °C
Country of Origin	China (CN)
Customs Tariff Number	85015100
Direction of Rotation	Both sides

Electrical Data				
Conn	Temp Class	Freq	Voltage	Power
D	--	50 Hz	380 V	7.50 kW
Frame Size	160			
IC Class	IC411			
IM Class	IMB3 IM1001			
Insulation Class	ICLF			
Invoice Description	M2BAX 160MLA6			
IP Class	IP55			
Made To Order	No			
Minimum Order Quantity	1 piece			
Number of Poles (High)	6			
Order Multiple	1 piece			
Package Level 1 Units	0 carton			
Product Name	3-Phase squirrel cage motor			
Product Type	CBA2__M2BAX_CI			
Quote Only	No			
Selling Unit of Measure	piece			
Standards	IEC 60034-1			
Starting of Motor	Direct Online			
Stocked At (Warehouses)	Shanghai, China			

Temperature Class	--
Default	
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	D
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)