


Standard Ex d Stopping Plug



Features

- Suitable for use in Zones 1, 2, 21, 22

Approvals



Certification & Standards

Approved to:	EN/IEC 60079-0, 60079-1
EC TYPE Examination Certificate:	Baseefa 08ATEX0324, IECEx BAS 08.0109 Ex d I Mb Ex d IIC Gb Ex tb IIIC Db UL1203 (Nickel Plated Brass and Stainless Steel only) Class I Div. 1 ABCD Class II Div. 1 EFG
Temperature:	-20°C bis +200°C

Nickel Plated Brass Part No.	Metric Thread	GID Code	Stainless Steel Part No.	Metric Thread	GID Code	Brass Part No.	Metric Thread	GID Code
EXN/M16/SP	M16 x 1.5	7TCA297140R0090	EXS/M16/SP	M16 x 1.5	7TCA297140R0157	EX/M16/SP	M16 x 1.5	7TCA297140R0036
EXN/M20/SP	M20 x 1.5	7TCA297140R0094	EXS/M20/SP	M20 x 1.5	7TCA297140R0118	EX/M20/SP	M20 x 1.5	7TCA297140R0042
EXN/M25/SP	M25 x 1.5	7TCA297140R0098	EXS/M25/SP	M25 x 1.5	7TCA297140R0121	EX/M25/SP	M25 x 1.5	7TCA297140R0050
EXN/M32/SP	M32 x 1.5	7TCA297140R0102	EXS/M32/SP	M32 x 1.5	7TCA297140R0122	EX/M32/SP	M32 x 1.5	7TCA297140R0058
EXN/M40/SP	M40 x 1.5	7TCA297140R0105	EXS/M40/SP	M40 x 1.5	7TCA297140R0123	EX/M40/SP	M40 x 1.5	7TCA297140R0064
EXN/M50/SP	M50 x 1.5	7TCA297140R0108	EXS/M50/SP	M50 x 1.5	7TCA297140R0124	EX/M50/SP	M50 x 1.5	7TCA297140R0068
EXN/M63/SP	M63 x 1.5	7TCA297140R0111	EXS/M63/SP	M63 x 1.5	7TCA297140R0168	EX/M63/SP	M63 x 1.5	7TCA297140R0072

Nickel Plated Brass Part No.	NPT Thread	GID Code	Stainless Steel Part No.	NPT Thread	GID Code	Brass Part No.	NPT Thread	GID Code
EXN/038/SP	3/8"	7TCA297140R0075	EXS/038/SP	3/8"	7TCA297140R0133	EX/038/SP	3/8"	7TCA297140R0019
EXN/050/SP	1/2"	7TCA297140R0077	EXS/050/SP	1/2"	7TCA297140R0113	EX/050/SP	1/2"	7TCA297140R0021
EXN/075/SP	3/4"	7TCA297140R0079	EXS/075/SP	3/4"	7TCA297140R0134	EX/075/SP	3/4"	7TCA297140R0024
EXN/100/SP	1"	7TCA297140R0081	EXS/100/SP	1"	7TCA297140R0123	EX/100/SP	1"	7TCA297140R0027
EXN/125/SP	1 1/4"	7TCA297140R0083	EXS/125/SP	1 1/4"	7TCA297140R0135	EX/125/SP	1 1/4"	7TCA297140R0029
EXN/150/SP	1 1/2"	7TCA297140R0085	EXS/150/SP	1 1/2"	7TCA297140R0114	EX/150/SP	1 1/2"	7TCA297140R0031
EXN/200/SP	2"	7TCA297140R0087	EXS/200/SP	2"	7TCA297140R0115	EX/200/SP	2"	7TCA297140R0033

CMG House, Station Road, Coleshill, Birmingham, B46 1HT United Kingdom

Tel: +44 (0) 1675 468 213 | Email: sales@kopex.co.uk

www.tnb-hazardous.com

The Company's policy is one of continuous improvement and reserves the right to change specifications at any time without prior notice.

Power and productivity
for a better world™

