

# E1N1000PR121/P- LSIGIn=1000A3pWMP

E1N 1000 PR121/P-LSIG In=1000A 3p W MP



## General Information

Extended Product Type	E1N1000PR121/P-LSIGIn=1000A3pWMP
Product ID	1SDA059222R1
EAN	8015644615833
Catalog Description	E1N 1000 PR121/P-LSIG In=1000A 3p W MP
Long Description	SACE EMAX MOVING PART FOR CIRCUIT-BREAKER E1N 1000A THRE-POLE OVERCURRENT RELEASE PR121/P-LSIG R1000 FITTED WITH: 4 AUXILIARY CONTACT AND C.BREAKER IN POSITION OPEN-CLOSED

## Ordering

EAN	8015644615833
Minimum Order Quantity	1 piece
Customs Tariff Number	85362090

## Dimensions

Product Net Width	324 mm
Product Net Height	461 mm
Product Net Depth / Length	396.5 mm
Product Net Weight	44 kg

## Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	515 mm
Package Level 1 Height	600 mm
Package Level 1 Depth / Length	515 mm
Package Level 1 Gross Weight	55 kg
Package Level 1 EAN	8015644609139

## Additional Information

Current Type	AC
Electrical Durability	Ue =< 440 V 10000 cycle Ue = 500 ... 690 V 8000 cycle 30 cycles per hour
Mechanical Durability	25000 cycle

	60 cycles per hour
Number of Poles	3
Power Loss	147.2 W
Product Main Type	SACE Emax
Product Name	Air Circuit Breaker
Product Type	Air Circuit Breaker
Rated Current ( $I_n$ )	1000 A
Rated Voltage ( $U_r$ )	690 V
Rated Impulse Withstand Voltage ( $U_{imp}$ )	12 kV
Rated Insulation Voltage ( $U_i$ )	1000 V
Rated Operational Current ( $I_e$ )	1000 A
Rated Operational Voltage	690 V AC
Rated Service Short-Circuit Breaking Capacity ( $I_{cs}$ )	(220 V AC) 50 kA (230 V AC) 50 kA (400 V AC) 50 kA (415 V AC) 50 kA (440 V AC) 50 kA (500 V AC) 50 kA (660 V AC) 50 kA (380 V AC) 50 kA (690 V AC) 50 kA
Rated Short-time Withstand Current ( $I_{cw}$ )	for 1 s 50 kA for 3 s 36 kA
Rated Ultimate Short-Circuit Breaking Capacity ( $I_{cu}$ )	(220 V AC) 50 kA (230 V AC) 50 kA (400 V AC) 50 kA (415 V AC) 50 kA (440 V AC) 50 kA (500 V AC) 50 kA (660 V AC) 50 kA (380 V AC) 50 kA (690 V AC) 50 kA
Rated Uninterrupted Current ( $I_u$ )	1000 A
Release Type	EL
Standards	IEC
Sub-type	E1
Terminal Connection Type	Withdrawable Circuit-Breakers
Version	W

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SDC200006D0209
Declaration of Conformity - CE	1SDL000165R0013
Environmental Information	1SDL000145R0
Instructions and Manuals	1SDH000460R0002

### Classifications

ETIM 4	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 5	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
ETIM 6	EC000228 - Power circuit-breaker for trafo/generator/installation prot.
Object Classification Code	Q
UNSPSC	39120000
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

—

### Categories

---

Low Voltage Products and Systems → Circuit Breakers → Air Circuit Breakers → Emax

