

PRODUCT-DETAILS

ACS355-03U-02A4-4+B063

ACS355-03U-03A3-4+B063, 480VAC, Pn 1HP,
I2LD 3.3A, IP66



General Information

| | |
|-------------------------|--|
| Global Commercial Alias | ACS355-03U-02A4-4+B063 |
| Product ID | 3AUA0000058140 |
| ABB Type Designation | ACS355-03U-02A4-4+B063 |
| EAN | 6438177224594 |
| Catalog Description | ACS355-03U-03A3-4+B063, 480VAC, Pn 1HP, I2LD 3.3A, IP66 |
| Long Description | The ACS355 drives are designed to meet the requirements of an extensive range of machinery applications in food and beverage, material handling, lifting, textile, printing, rubber and plastics, and woodworking applications. The drive is user-friendly, yet it provides a wide range of built-in technology such as the safe torque off functionality and sequence programming, reducing the need for additional control electronics. The product offers options and diverse functionality to cater to the needs set for speed and torque control of AC induction and permanent magnet motors. |

Ordering

| | |
|------------------------|---|
| Country of Origin | China (CN) |
| Customs Tariff Number | 85044080 |
| Invoice Description | ACS355-03U-03A3-4+B063, 480VAC, Pn 1HP, I2LD 3.3A, IP66 |
| Made To Order | No |
| Minimum Order Quantity | 1 piece |
| Order Multiple | 1 piece |
| Quote Only | No |

Selling Unit of Measure

piece

Dimensions

| | |
|----------------------------|----------|
| Product Net Weight | 17.4 lb |
| Product Net Depth / Length | 11.06 in |
| Product Net Height | 12 in |
| Product Net Width | 7.68 in |

Technical

| | |
|---|---------------|
| Number of Phases | 3 |
| Degree of Protection | IP66 |
| Enclosure Type NEMA | Type4X |
| Frequency (f) | 50/60 Hz |
| Frame Size | R1 |
| Input Voltage (U _{in}) | 380 ... 480 V |
| Mounting Type | Wall-mounting |
| Output Current, Normal | 3 A |
| Use (I _n) | |
| Output Power, Light-Overload Use (P _{LD}) | 1 Hp |
| Output Power, Normal | 1 Hp |
| Use (P _n) | |

Additional Information

| | |
|--------------|----------|
| Product Name | AC Drive |
|--------------|----------|

Classifications

| | |
|--------|----------|
| UNSPSC | 39122001 |
|--------|----------|

Environmental

| | |
|---------------|--|
| SCIP | 1d727ac6-731e-434d-a73b-9a3611c425ac Finland (FI) |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |

Categories

Drives → Low Voltage AC Drives → Machinery Drives → ACS355 - Machinery Drive

