

PRODUCT-DETAILS

ACS355-03E-15A6-4 Solar Pump Drive

ACS355-03E-15A6-4 Solar Pump Drive; ACS355-03E-15A6-4 Pn 5,5kW, I2n 15,6A IP20 Solar Pump Drive



General Information

Global Commercial Alias	ACS355-03E-15A6-4 Solar Pump Drive
Product ID	3AUA0000157195
ABB Type Designation	ACS355-03E-15A6-4 Solar Pump Drive
EAN	6438177325086
Catalog Description	ACS355-03E-15A6-4 Solar Pump Drive; ACS355-03E-15A6-4 Pn 5,5kW, I2n 15,6A IP20 Solar Pump Drive
Long Description	<p>The ACS355 drives are designed to meet the requirements of an extensive range of machinery applications in food and beverage, material handling, lifting, textile, printing, rubber and plastics, and woodworking applications.</p> <p>The drive is user-friendly, yet it provides a wide range of built-in technology such as the safe torque off functionality and sequence programming, reducing the need for additional control electronics. The product offers options and diverse functionality to cater to the needs set for speed and torque control of AC induction and permanent magnet motors.</p>

Ordering

Country of Origin	China (CN) Finland (FI)
Customs Tariff Number	85044085
Invoice Description	ACS355-03E-15A6-4 Pn 5,5kW, I2n 15,6A IP20 Solar Pump Drive
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	3.3 kg
Product Net Depth / Length	169 mm
Product Net Height	236 mm
Product Net Width	169 mm
Package Level 1 Depth / Length	344 mm
Package Level 1 Height	226 mm
Package Level 1 Width	217 mm
Package Level 1 Units	1 carton

Technical	
Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	50/60 Hz
Frame Size	R3
Input Voltage (U_{in})	380 ... 480 V
Mounting Type	Module for cabinet building
Output Current, Normal Use (I_n)	15.6 A
Output Power, Normal Use (P_n)	7.5 kW

Additional Information	
Product Main Type	ACS355
Product Name	Solar frequency converter

Classifications	
ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Kit Contents			
Identifier	Description	Quantity	Unit Of Measure
3AUA0000058191	ACS355-03E-15A6-4 Pn 7,5kW, I2n 15,6A IP20	1	piece
3AUA0000150422		1	

Categories

Drives → Low Voltage AC Drives → Machinery Drives → ACS355 - Machinery Drive

Drives → Services → Spares and Consumables → Parts

