

PRODUCT-DETAILS

ACS355-03E-08A8-4+B063 Solar Pump D
ACS355-03E-08A8-4+B063 Solar Pump D;
ACS355-03E-08A8-4+B063 Pn 3kW, I2n 8,8A
IP66 Solar Pump Drive



General Information

Global Commercial Alias	ACS355-03E-08A8-4+B063 Solar Pump D
Product ID	3AUA0000157213
ABB Type Designation	ACS355-03E-08A8-4+B063 Solar Pump D
EAN	6438177325260
Catalog Description	ACS355-03E-08A8-4+B063 Solar Pump D; ACS355-03E-08A8-4+B063 Pn 3kW, I2n 8,8A IP66 Solar Pump Drive
Long Description	<p>The ACS355 drives are designed to meet the requirements of an extensive range of machinery applications in food and beverage, material handling, lifting, textile, printing, rubber and plastics, and woodworking applications.</p> <p>The drive is user-friendly, yet it provides a wide range of built-in technology such as the safe torque off functionality and sequence programming, reducing the need for additional control electronics. The product offers options and diverse functionality to cater to the needs set for speed and torque control of AC induction and permanent magnet motors.</p>

Ordering

Country of Origin	China (CN) Finland (FI)
Customs Tariff Number	85044085
Invoice Description	ACS355-03E-08A8-4+B063 Pn 3kW, I2n 8,8A IP66 Solar Pump Drive
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	8.4 kg
Product Net Depth / Length	281 mm
Product Net Height	346 mm
Product Net Width	195 mm
Package Level 1 Depth / Length	790 mm
Package Level 1 Height	255 mm
Package Level 1 Width	345 mm
Package Level 1 Units	1 carton

Technical	
Number of Phases	3
Degree of Protection	IP66
Enclosure Type NEMA	Type4X
Frequency (f)	50/60 Hz
Frame Size	R1
Input Voltage (U_{in})	380 ... 480 V
Mounting Type	Module for cabinet building
Output Current, Normal Use (I_n)	8.8 A
Output Power, Normal Use (P_n)	4 kW

Additional Information	
Product Main Type	ACS355
Product Name	Solar frequency converter

Classifications	
ETIM 8	EC001857 - Frequency converter =< 1 kV
ETIM 9	EC001857 - Frequency converter =< 1 kV
UNSPSC	39122001

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Kit Contents			
Identifier	Description	Quantity	Unit Of Measure
3AUA0000058163	ACS355-03E-08A8-4+B063 Pn 4, I2n 8,8A IP66.	1	piece
3AUA0000150422		1	

Categories

Drives → Low Voltage AC Drives → Machinery Drives → ACS355 - Machinery Drive

Drives → Services → Spares and Consumables → Parts

