




PRODUCT-DETAILS

3GAA091520-JSJ436

IE3 Premium Efficiency Aluminum Motors, 2.2 kW, 400 V (3GAA091520-JSJ436)



General Information	
Product ID	3GAA091520-JSJ436
ABB Type Designation	M3AA 90LB 2
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 2.2 kW, 400 V (3GAA091520-JSJ436)

Ordering	
ABB Type Designation	M3AA 90LB 2
Invoice Description	M3AA 90LB 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA0__M3AA_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Romania (RO)
Customs Tariff Number	85015220

Electrical	
Electrical Data	

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	2.20 kW	2903 r/min	4.70 A	0.790	85.90 %	7.20 N·m	7.40
D	--	50 Hz	230 V	2.20 kW	2902 r/min	8.20 A	0.790	85.90 %	7.24 N·m	7.40
Y	--	50 Hz	415 V	2.20 kW	2911 r/min	4.80 A	0.750	85.90 %	7.20 N·m	7.60
Connection Configuration										Y
Temperature Class										--
Default										
Input Voltage (U _{in})										400 V
Frequency (f)										50 Hz
Output Power										2.2 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE3 Full Load (100%) 85.9 % Partial Load (75%) 85.8 % Partial Load (50%) 83.8 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										2
Two Speed Motor										No
Type of Duty										S1
Voltage Code										S

Mechanical

Frame Material	Aluminum
Frame Size	90
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
IM Class	IMB34 IM2101
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	331.5 mm
Product Net Height	217 mm
Product Net Width	170 mm
Product Net Weight	17 kg
Gross Weight	24 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

