


PRODUCT-DETAILS

3GAA092540-HSJ

IE3 Premium Efficiency Aluminum Motors, 1.5 kW, 400 V (3GAA092540-HSJ)



General Information	
Product ID	3GAA092540-HSJ
ABB Type Designation	M3AA 90LD 4
Catalog Description	IE3 Premium Efficiency Aluminum Motors, 1.5 kW, 400 V (3GAA092540-HSJ)

Ordering	
ABB Type Designation	M3AA 90LD 4
Invoice Description	M3AA 90LD 4
Product Name	3-Phase squirrel cage motor
Product Type	3AA0__M3AA_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015220
Medium Description	1.5kW, 4 Poles, Frame Size 90, 3 Phases, 400V, 50Hz, IP55 Enclosure, IMB35/IM2001 Mounting (3GAA092540-HSJ)
Short Description	1.5kW, 4P, Frame Size 90, 3PH, 400V, 50Hz, IP55, IMB35/IM2001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	1.50 kW	1445 r/min	3.34 A	0.750	85.30 %	9.95 N·m	7.60
D	--	50 Hz	230 V	1.50 kW	1445 r/min	5.85 A	0.750	85.30 %	9.95 N·m	7.60
Y	--	50 Hz	415 V	1.50 kW	1450 r/min	3.24 A	0.750	85.30 %	9.95 N·m	7.60

Connection Configuration	Y
Temperature Class Default	--
Input Voltage (U _{in})	400 V
Frequency (f)	50 Hz
Output Power	1.5 kW
Altitude	1000 m
Ambient Temperature	40 °C
IC Class	IC411
IE Class Data (50 Hz)	IE Class IE3 Full Load (100%) 85.3 % Partial Load (75%) 84.7 % Partial Load (50%) 82.1 %
IP Class	IP55
Insulation Class	ICLF
Direction of Rotation	Both sides
Number of Poles (High)	4
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Frame Material	Aluminum
Frame Size	90
Bearing	6205-2Z/C3
Bearing NDE	6204-2Z/C3
IM Class	IMB35 IM2001
Terminator Box Location	D-End top

Package Level 1 Units	0 carton
Product Net Depth / Length	331.5 mm
Product Net Height	217 mm
Product Net Width	170 mm
Product Net Weight	20 kg
Gross Weight	23 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
	39120000

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

