


PRODUCT-DETAILS

3GAL132247-BFC

IE5 SynRM Motors, 15 kW, 380 V (3GAL132247-BFC)



General Information	
Product ID	3GAL132247-BFC
ABB Type Designation	M3AL 132SMD 4
Catalog Description	IE5 SynRM Motors, 15 kW, 380 V (3GAL132247-BFC)

Ordering	
ABB Type Designation	M3AL 132SMD 4
Invoice Description	M3AL 132SMD 4
Product Name	3Phase Synchronous reluctance motor
Product Type	3AL4__M3AL_IE5_SynRM_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI)
Customs Tariff Number	85015230
Medium Description	15kW, 4 Poles, Frame Size 132, 3 Phases, 380V, 50Hz, IP55 Enclosure, IMB5/IM3001 Mounting (3GAL132247-BFC)
Short Description	15kW, 4P, Frame Size 132, 3PH, 380V, 50Hz, IP55, IMB5/IM3001

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	500 V	15.00 kW	3000 r/min	26.60 A	0.740	94.10 %	47.75 N·m	0.00
Connection Configuration										Y
Temperature Class Default										--
Input Voltage (U _{in})										380 V
Frequency (f)										50 Hz
Output Power										15 kW
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE5
										Full Load (100%) 94.1 %
										Partial Load (75%) 93.6 %
										Partial Load (50%) 91.9 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										4
Two Speed Motor										No
Type of Duty										S9
Voltage Code										F

Mechanical

Frame Material	Aluminum
Frame Size	132
Bearing	6308-2Z/C3
Bearing NDE	6206-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Depth / Length	487 mm
Product Net Height	296 mm
Product Net Width	262 mm
Product Net Weight	47 kg
Gross Weight	52 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Synchronous Reluctance Motors → IE5 SynRM Motors

