


PRODUCT-DETAILS

3GAA131120-ASK843 (3GAA131120-ASK843)



General Information

Product ID	3GAA131120-ASK843
ABB Type Designation	M3AA 132SB 2
Catalog Description	(3GAA131120-ASK843)

Ordering

ABB Type Designation	M3AA 132SB 2
Invoice Description	M3AA 132SB 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA3_M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Romania (RO)
Customs Tariff Number	85015220
Stocked At (Warehouses)	Menden, Germany

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	400 V	5.50 kW	2901 r/min	9.70 A	0.910	89.20 %	18.10 N·m	7.90
D	--	50 Hz	230 V	5.50 kW	2901 r/min	16.80 A	0.910	89.20 %	18.10 N·m	7.90
Y	--	50 Hz	380 V	5.50 kW	2886 r/min	10.30 A	0.920	89.20 %	18.06 N·m	7.10
D	--	50 Hz	220 V	5.50 kW	2886 r/min	17.80 A	0.920	89.20 %	18.06 N·m	7.10
Y	--	50 Hz	415 V	5.50 kW	2911 r/min	9.40 A	0.910	89.20 %	18.10 N·m	8.50
Temperature Class										--
Default										
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE3 Full Load (100%) 89.2 % Partial Load (75%) 89.7 % Partial Load (50%) 89.8 %
IE Class Data (60 Hz)										IE Class IE3 Full Load (100%) 89.5 % Partial Load (75%) 89.4 % Partial Load (50%) 88.7 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										2
Two Speed Motor										No
Type of Duty										S1
Voltage Code										S

Mechanical

Frame Material	Aluminum
Frame Size	132
Bearing	6208-2Z/C3
Bearing NDE	6206-2Z/C3
IM Class	IMB3 IM1001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	58 kg
Gross Weight	63 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

