

# F204 A-40/0,03



## F204 A-40/0,03 Residual Current Circuit Breaker



### Informations générales

Extended Product Type	F204 A-40/0,03
Id du produit	2CSF204101R1400
EAN	8012542783503
Description catalogue	F204 A-40/0,03 Residual Current Circuit Breaker
Description	The RCCBs F200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous and selective AC and A types is completed with some configurations for special applications.

### Technical

Standards	IEC/EN 61008 UL 1053
Operating Characteristic	Instantaneous
Type of Residual Current	A type
Rated Residual Current	30 mA
Rated Current ( $I_n$ )	40 A
Nombre de pôles	4
Position of Neutral Terminals	Right
Power Loss	at Rated Operating Conditions per Pole 3.2 W
Rated Voltage ( $U_r$ )	230/400 V
Fréquence assignée (f)	50...60 Hz

### Environmental

Température de l'air ambiant	Operation -25 ... +55 °C Storage -40 ... +70 °C
RoHS Status	Following EU Directive 2011/65/EU

### Technical UL/CSA

Maximum Operating Voltage UL/CSA	480Y / 277 V AC
Short-Circuit Current Rating (SCCR)	0.03 mA

### Dimensions

Product Net Width	0.070 m
-------------------	---------

---

Product Net Height	0.085 m
Product Net Depth / Length	0.069 m
Poids net	0.360 kg

---

---

## Container Information

---

Niveau de l'unité d'emballage 1	1 piece
Package Level 1 Width	0.082 m
Package Level 1 Height	0.078 m
Package Level 1 Depth / Length	0.096 m
Package Level 1 Gross Weight	0.403 kg
Package Level 1 EAN	8012542783503

---

---

## Ordering

---

Quantité minimum	1 piece
Nombre des douanes tarif	85363030

---

---

## Certificates and Declarations (Document Number)

---

Declaration of Conformity - CE	9AKK106713A5602
Environmental Information	Refer to RoHS
Instructions and Manuals	Manual sheet inside the box
RoHS Information	2CSC423001K2702

---

---

## Downloads Préférés

---

Data Sheet, Technical Information	9AKK107046A0424
Instructions and Manuals	Manual sheet inside the box

---

---

## Classifications

---

Object Classification Code	Q
ETIM 4	EC000003 - Residual current circuit breaker (RCCB)
ETIM 5	EC000003 - Residual current circuit breaker (RCCB)
ETIM 6	EC000003 - interrupteur différentiel
ETIM 7	EC000003 - Residual current circuit breaker (RCCB)

---

---

## Catégories

---

Produits basse tension → Appareillage modulaire et parafoudres → Protection différentielle → Interrupteurs différentiels

