

# 限用物質含有情況標示樣張

Sample of the Presence Condition of the Restricted Substances Marking

證書號碼／受理編號：(No.) CI315067070277  
Certificate No./Application No.

設備名稱：無熔線斷路器 Moulded Case Circuit Breaker 型號（型式）：SH204 4P 63AF Equipment name Type designation (Type)						
SH204 4P 63AF 50/60Hz Icn=Ics 6kA at 220V B6, B10, B13, B16, B20, B25, B32, B40, B50, B63, C0.5, C1, 1.6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63, D0.5, D1, D1.6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63						
單元 Unit	限用物質及其化學符號 Restricted substances and its chemical symbols					
	鉛Lead (Pb)	汞Mercury (Hg)	鎘Cadmium (Cd)	六價鉻Hexavalent chromium (Cr <sup>+6</sup> )	多溴聯苯Polybrominated biphenyls (PBB)	多溴二苯醚Polybrominated diphenyl ethers (PBDE)
外殼(Housing)	○	○	○	○	○	○
切換機構(Switching mechanism)	○	○	○	○	○	○
電磁跳脫裝置(Magnetic release)	超出 0.1 wt %	○	○	○	○	○
積熱跳脫裝置(Thermal release)	○	○	○	○	○	○
消弧系統(Arc extinguishing system)	○	○	○	○	○	○
接線端子(Terminals)	○	○	○	○	○	○
塑料部件(Other plastic components)	○	○	○	○	○	○
備考1. “超出0.1 wt %” 及 “超出0.01 wt %” 係指限用物質之百分比含量超出百分比含量基準值。 Note 1: “Exceeding 0.1 wt %” and “exceeding 0.01 wt %” indicate that the percentage content of the restricted substance exceeds the reference percentage value of presence condition.						
備考2. “○” 係指該項限用物質之百分比含量未超出百分比含量基準值。 Note 2: “○” indicates that the percentage content of the restricted substance does not exceed the percentage of reference value of presence.						
備考3. “—” 係指該項限用物質為排除項目。 Note 3: The “—” indicates that the restricted substance corresponds to the exemption.						

系列型式：

## SH201 (1P), 63AF, Icn=Ics, 6kA at 220V

B6, B10, B13, B16, B20, B25, B32, B40, B50, B63 C0.5, C1, C1.6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63 D0.5, D1, D1.6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63

## SH201 (1P+N), 63AF, Icn=Ics, 6kA at 220V

B6, B10, B13, B16, B20, B25, B32, B40, B50, B63 C0.5, C1, C1.6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63 D0.5, D1, D1.6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63

**SH202 (2P), 63AF, Icn=Ics, 6kA at 220V**

B6, B10, B13, B16, B20, B25, B32, B40, B50, B63 CO. 5, C1, C1. 6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63 DO. 5, D1, D1. 6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63

**SH203 (3P), 63AF, Icn=Ics, 6kA at 220V**

B6, B10, B13, B16, B20, B25, B32, B40, B50, B63 CO. 5, C1, C1. 6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63 DO. 5, D1, D1. 6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63

**SH203 (3P+N), 63AF, Icn=Ics, 6kA at 220V**

B6, B10, B13, B16, B20, B25, B32, B40, B50, B63 CO. 5, C1, C1. 6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63 DO. 5, D1, D1. 6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63