

限用物質含有情況標示聲明書

Declaration of the Presence Condition of the Restricted Substances Marking

證書號碼／受理編號：(No.) TA114317070154-00

Certificate No./Application No.

商品標籤及商品檢驗標識：如圖標示

Product Label and Commodity Inspection Mark.

樣張及其標示位置：如圖標示

Sample and its location

設備名稱：無熔線斷路器 Moulded Case Circuit Breaker 型號（型式）： S204M
Equipment name Type designation (Type)

S204M 4P 63AF 60Hz Icn: 10kA at 380V, Ics:7.5kA at 380V

B6, B10, B13, B16, B20, B25, B32, B40, B50, B63, C0. 5, C1, 1. 6, C2, C3, C4, C6, C8, C10, C13, C16, C20,

C25, C32, C40, C50, C63, D0. 5, D1, D1. 6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63

單元 Unit	限用物質及其化學符號 Restricted substances and its chemical symbols					
	鉛Lead (Pb)	汞Mercury (Hg)	鎘Cadmium (Cd)	六價鉻 Hexavalent chromium (Cr ⁺⁶)	多溴聯苯 Polybrominated biphenyls (PBB)	多溴二苯醚 Polybrominated diphenyl ethers (PBDE)
外殼(Housing)	O	O	O	O	O	O
切換機構(Switching mechanism)	O	O	O	O	O	O
電磁跳脫裝置 (Magnetic release)	超出 0.1 wt %	O	O	O	O	O
積熱跳脫裝置 (Thermal release)	O	O	O	O	O	O
消弧系統(Arc extinguishing system)	O	O	O	O	O	O
接線端子(Terminals)	O	O	O	O	O	O
塑料部件(Other plastic components)	O	O	O	O	O	O

備考1. “超出0.1 wt %”及“超出0.01 wt %”係指限用物質之百分比含量超出百分比含量基準值。

Note 1: “Exceeding 0.1 wt %” and “exceeding 0.01 wt %” indicate that the percentage content of the restricted substance exceeds the reference percentage value of presence condition.

備考2. “○”係指該項限用物質之百分比含量未超出百分比含量基準值。

Note 2: “○” indicates that the percentage content of the restricted substance does not exceed the percentage of reference value of presence.

備考3. “—”係指該項限用物質為排除項目。

Note 3: The “—” indicates that the restricted substance corresponds to the exemption.

系列型式：

S201M 1P, 63AF, 60Hz I_{cn}: 10kA at 220V/380V, I_{cs}:7.5kA at 220V/380V
B6, B10, B13, B16, B20, B25, B32, B40, B50, B63
C0.5, C1, C1.6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63
D0.5, D1, D1.6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63

S201M-NA 1P+N, 63AF, 60Hz I_{cn}: 10kA at 220V, I_{cs}:7.5kA at 220V
B6, B10, B13, B16, B20, B25, B32, B40, B50, B63
C0.5, C1, C1.6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63
D0.5, D1, D1.6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63

S202M 2P, 63AF, 60Hz I_{cn}: 10kA at 380V, I_{cs}:7.5kA at 380V
B6, B10, B13, B16, B20, B25, B32, B40, B50, B63
C0.5, C1, C1.6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63
D0.5, D1, D1.6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63

S203M 3P, 63AF, 60Hz I_{cn}: 10kA at 380V, I_{cs}:7.5kA at 380V
B6, B10, B13, B16, B20, B25, B32, B40, B50, B63
C0.5, C1, C1.6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63
D0.5, D1, D1.6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63

S203M-NA 3P+N 63AF, 60Hz I_{cn}: 10kA at 380V, I_{cs}:7.5kA at 380V
B6, B10, B13, B16, B20, B25, B32, B40, B50, B63
C0.5, C1, C1.6, C2, C3, C4, C6, C8, C10, C13, C16, C20, C25, C32, C40, C50, C63
D0.5, D1, D1.6, D2, D3, D4, D6, D8, D10, D13, D16, D20, D25, D32, D40, D50, D63